

# ELASTECH

UER125X40-Ø15

EAN 4031582337952



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●●●

Ishrana ●●●○○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda	Elastech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	250 kg
Statički Nosivost	500 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0,429 kg

## TOCAK

Materijal za telo	poliamid
materijal omotaca	Elastična guma, crna, vulkanizovana
Nošenje	kotrljajući lezaj
stitnici omotaca	Bez stražara
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	15 mm
dužina glavcine	58 mm

# ELASTECH

UER125X40-Ø15

EAN 4031582337952



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

---

