

MAXTECH

UAP 125x40-Ø20 HL60 natural/3004

EAN 4031582322965



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Tip	Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	300 kg
Nosivost na 6 km/h	300 kg
Električni provod	no
nerdjajuci	no
Statički Nosivost	600 kg
Temperaturni opseg (Minimalno)	-25 °C
Opseg temperature (maksimalni)	80 °C
Ukupna težina	0.66 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Poliuretan, liveno
Nošenje	precizini kuglicni lezaj
Boja Tocak	Prirodno belo
stitnici omotaca	Sa threadguard
Prečnik	125 mm
Širina omotac	40 mm
dimenzija rupa osovina	20 mm
dužina glavnice	60 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	96 Šešelj A
Teškoća gazećeg omotac (D)	48 Šor D

MAXTECH

UAP 125x40-Ø20 HL60 natural/3004

EAN 4031582322965

Broj porudžbine 00034205
Product Drawings



BETTER MOBILITY. BETTER LIFE.

