

# STORA

2370PHP125P30-11

EAN 4031582364972



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Stora
Housing type	Swivel castor
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	155 mm
Overall weight	0.672 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber, antistatic
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	125 mm
Tread width	32 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Slim
Swivel bearing	Two ball races
Offset	38 mm
Swivel radius	100.5 mm
Swivel interference	201 mm

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	11 mm

# STORA

2370PHP125P30-11

EAN 4031582364972



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

