

# DURATECH

TOP 085X95-Ø20 HL97

EAN 4031582334234  
Order number 00839855



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	85 mm
Tread width	95 mm
Axle hole diameter	20 mm
Hub length	97 mm
Body width	95 mm
Hardness of tread (D)	75 Shore D
Bearing type	6204ZV

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Duratech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	900 kg
Load capacity at 6 km/h	720 kg
Load capacity Static	1800 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall weight	0.569 kg

# DURATECH

TOP 085X95-Ø20 HL97

EAN 4031582334234  
Order number 00839855



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

