

AGILA STAINLESS

7477PJO150P51

EAN 4031582350500



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●●

OSNOVNI ATRIBUTI

Naziv proizvoda	Agila stainless
Tip	Okreni Tocak sa potpuna kocnica
Standard	EN12530 - Kastori uređaja
Nosivost na 3 km/h	100 kg
nerdjajuci	✓
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	183 mm
Ukupna težina	0,952 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Termoplastična guma
Nošenje	klizni lezaj
stitnici omotaca	Bez stražara
Prečnik	150 mm
Širina omotac	32 mm
Teškoća gazećeg omotac (A)	87 Šora A

KUCISTE

Materijal	nerdjajuci čelik, medijum
oblik viljuska	siroko
okretni lezaj	Dve lopte
ofset	36 mm
Otpor okretanju	262 mm

PRILAGOĐAVANJE

Tip uklapanja	Pravougaona ploča
Dužina ploče	95 mm
Širina ploče	70 mm
Dužina otvora ploče (maksimalna)	75 mm
Širina otvora ploče (maksimalna)	50 mm
Prečnik otvora ploče	11 mm

AGILA STAINLESS

7477PJO150P51

EAN 4031582350500



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

