

PRODUCT INFORMATION

P10-40X27 / 8

EAN 4031582320152



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 1.8 mph	88.18 lb
Load capacity Static	176.37 lb
Overall height	0.31 in

FITTING

Fitting type	Stem with U-shaped plate
Plate length	1.57 in
Plate width	1.06 in
Plate hole length (Maximum)	1.26 in
Plate hole width (Maximum)	1.26 in
Plate hole diameter	0.16 in