

NOVATECH

ITP 125X30-Ø15 HL45

EAN 4031582319873
Order number 00829478



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	30 mm
Axle hole diameter	15 mm
Hub length	45 mm
Body width	30 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	420 kg
Load capacity at 6 km/h	335 kg
Load capacity Static	840 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	0.48 kg

NOVATECH

ITP 125X30-Ø15 HL45

EAN 4031582319873
Order number 00829478



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

