

# DURATECH

TOP 085X95-Ø20 HL97

EAN 4031582334234  
 订单号 00839855



BETTER MOBILITY. BETTER LIFE.



图片可能与原产品不同

## 轮子

轮体材料	聚酰胺，重
胎面材料	与轮子体相同
轴承	精密滚珠轴承
轮子颜色	天然白色
侧盖	无螺纹护罩
直径	85 mm
胎面宽度	95 mm
轴孔直径	20 mm
中心长度	97 mm
轮体宽度	95 mm
胎面硬度 (D)	75 岸 D
轴承类型	6204ZV

## 表现

滚动性能	● ● ● ● ●
运动噪音	● ● ○ ○ ○
损耗	● ● ● ● ●
耐腐蚀性	● ● ● ○ ○

## 核心属性

产品名称	Duratech
标准	EN12533 - 重载脚轮
4 公里/小时的载重	900 kg
6 公里/小时的载重	720 kg
静态载重	1800 kg
温度范围 (最低)	-40 ° C
温度范围 (最大)	80 ° C
总重量	0.569 kg

# DURATECH

TOP 085X95-Ø20 HL97

EAN 4031582334234  
订单号 00839855



BETTER MOBILITY. BETTER LIFE.

## 技术图纸

