

# COMPACTA

2198UOI025P60-40x17

EAN 4031582300284



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Compacta                  |
| Type                        | Fixed castor              |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 25 kg                     |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 50 kg                     |
| Temperature range (Minimum) | -25 °C                    |
| Temperature range (Maximum) | 80 °C                     |
| Overall Height              | 28 mm                     |
| Overall width               | 20 mm                     |
| Overall weight              | 0.02 kg                   |

## HOUSING

|                  |                     |
|------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape       | Angular             |
| Housing Color    | Blue passivated     |
| Dome diameter    | 20 mm               |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread Material Mix    | Identical with wheel body      |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Wheel Color           | Graphite black (RAL9011)       |
| Threadguards          | Without threadguard            |
| Diameter              | 25 mm                          |
| Tread width           | 13 mm                          |
| Body width            | 13 mm                          |
| Hardness of tread (D) | 75 Shore D                     |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 40 mm             |
| Plate width                 | 17 mm             |
| Plate hole length (Maximum) | 30 mm             |
| Plate hole width (Maximum)  | 30 mm             |
| Plate hole diameter         | 4.5 mm            |

# COMPACTA

2198UOI025P60-40x17

EAN 4031582300284

Order number 00021131

Product Drawings



BETTER MOBILITY. BETTER LIFE.

