


NOVATECH

RK.ETP085X80-Ø47X15,5

EAN 4031582369571



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Nedefinisani
materijal omotaca	polipropilen, mekan
Prečnik	85 mm
Širina omotac	80 mm
Teškoća gazećeg omotac (A)	92 Šor A
Prečnik kuglicni lezaj	47 mm
Širina kuglicni lezaj	15,5 mm

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Novatech
Tip	Tocak
Nosivost na 3 km/h	800 kg
Statički Nosivost	1600 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C

TEHNIČKI CRTEŽI

