

# FOOTMASTER

FOOT MASTER GAAD-150-ASF-HUD

EAN 4031582495188  
Order number 00800111



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

## CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 1.8 mph	1388.91 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	194 °F
Overall height	8.46 in
Overall width	5.55 in
Overall weight	33.49 lb

## WHEEL

Bearing	Unmachined hub
Diameter	5.91 in
Tread width	1.38 in
Body width	1.38 in

## HOUSING

Offset	1.38 in
Swivel radius	4.53 in
Swivel interference	9.06 in
Dome diameter	5.04 in

## FITTING

Plate length	5.71 in
Plate width	5.71 in
Plate hole length (Maximum)	4.72 in
Plate hole width (Maximum)	4.72 in
Plate hole diameter	0.43 in

# FOOTMASTER

FOOT MASTER GAAD-150-ASF-HUD

EAN 4031582495188  
Order number 00800111



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

