

MAXTECH

PNP 200X30-Ø8 HL44

EAN 4031582320626

Broj porudžbine 00005568



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Poliuretanski, penasti
Nošenje	precizini kuglicni lezaj
Boja Tocak	Crna
stitnici omotaca	Sa threadguard
Prečnik	200 mm
Širina omotac	30 mm
dimenzija rupa osovina	8 mm
dužina glavcine	44 mm
Širina tela	30 mm
Teškoća gazećeg omotac (A)	70 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Maxtech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	100 kg
Statički Nosivost	200 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,4 kg

MAXTECH

PNP 200X30-Ø8 HL44

EAN 4031582320626

Broj porudžbine 00005568



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

