

DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1587.33 lb
Load capacity at 3.7 mph	1322.77 lb
Electric conductive	no
Stainless	no
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.84 lb

DURATECH

TOO 100x50-Ø20 HL60


EAN 4031582322491

Order number 00804809

Product Drawings



BETTER MOBILITY. BETTER LIFE.




PRODUCT INFORMATION

DURATECH

TOO 100x50-Ø20 HL50

EAN 4031582322494

Order number 00804809



BETTER MOBILITY. BETTER LIFE.