PRODUCT INFORMATION

DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●●●
Movement noise	●●○○○
Attrition	●●●●●
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1587.33 lb
Load capacity at 3.7 mph	1322.77 lb
Electric conductive	no
Stainless	no
Load capacity Static	2645.54 lb
Temperature range (Minimum)	-40 °F
Temperature range (Maximum)	176 °F
Overall weight	0.84 lb

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Wheel color	Natural white
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (D)	75 Shore D


DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491

Order number 00804809

Product Drawings




© Copyright 2026 TENTE International GmbH

DURATECH

TOO 100x50-Ø20 HL60

EAN 4031582322491

Order number 00804809



© Copyright 2026 TENTE International GmbH