

KAPPA LOAD

9651FTP200P64 CL97

EAN 4031582314489
Order number 00863070



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	1680 kg
Load capacity at 6 km/h	1400 kg
Load capacity Static	2800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	255 mm
Overall width	140 mm
Overall weight	13.376 kg

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	200 mm
Tread width	80 mm
Body width	80 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Colour	Zink-iron (transparent)
Offset	65 mm
Swivel radius	170 mm
Swivel interference	340 mm
Dome diameter	140 mm

FITTING

Fitting type	Rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Maximum)	140 mm
Plate hole diameter	15 mm

KAPPA LOAD

9651FTP200P64 CL97

EAN 4031582314489
Order number 00863070



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

