

PRODUCT INFORMATION

NOVATECH

FTP 150x60-Ø25 HL60

EAN 4031582329520



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES


Product Name	Novatech
Type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Electric Conductive	No
Stainless	No
Load capacity Static	1600 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	3.94 kg



BETTER MOBILITY. BETTER LIFE.

WHEEL

Body material	Cast iron
Tread Material Mix	Polyurethane, casted
Bearing	Precision ball bearing
Wheel Color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	150 mm
Tread width	60 mm
Axle Hole Diameter	25 mm
Hub Length	60 mm
Body width	60 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D




PRODUCT INFORMATION

NOVATECH

FTP 150x60-025 H160

EAN 4031582389520

Order number 10827815



BETTER MOBILITY. BETTER LIFE.