

# PURETECH

FVP 200X75-Ø20 HL90

EAN 4031582319514  
Order number 00801897



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Cast iron
Tread material	Solid rubber, black
Bearing	Precision ball bearing
Wheel color	Jet black (similar RAL9005)
Threadguards	With threadguard
Diameter	200 mm
Tread width	75 mm
Axle hole diameter	20 mm
Hub length	90 mm
Body width	75 mm
Hardness of tread (A)	67 Shore A

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Puretech
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	600 kg
Load capacity at 6 km/h	500 kg
Load capacity Static	1000 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	5.911 kg

# PURETECH

FVP 200X75-Ø20 HL90

EAN 4031582319514  
Order number 00801897



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

