

DURATECH

TOP 085X100-Ø20 HL100

EAN 4031582331301
 订单号 00832618



BETTER MOBILITY. BETTER LIFE.



图片可能与原产品不同

轮子

轮体材料	聚酰胺，重
胎面材料	与轮子体相同
轴承	精密滚珠轴承
轮子颜色	天然白色
侧盖	无螺纹护罩
直径	85 mm
胎面宽度	100 mm
轴孔直径	20 mm
中心长度	100 mm
轮体宽度	100 mm
胎面硬度 (D)	75 岸 D
轴承类型	6204

表现

滚动性能	● ● ● ● ●
运动噪音	● ● ○ ○ ○
损耗	● ● ● ● ●
耐腐蚀性	● ● ● ○ ○

核心属性

产品名称	Duratech
标准	EN12533 - 重载脚轮
4 公里/小时的载重	900 kg
6 公里/小时的载重	720 kg
静态载重	1800 kg
温度范围 (最低)	-40 ° C
温度范围 (最大)	80 ° C
总重量	0.585 kg

DURATECH

TOP 085X100-Ø20 HL100

EAN 4031582331301
订单号 00832618



BETTER MOBILITY. BETTER LIFE.

技术图纸

