

NOVATECH

ITP250X50-Ø20 HL60 SUPER CONVEX R25

EAN 4031582444681



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminium
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	20 mm
Hub length	60 mm
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	800 kg
Load capacity Static	1600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	2.181 kg

NOVATECH

ITP250X50-Ø20 HL60 SUPER CONVEX R25

EAN 4031582444681



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

