

NOVATECH

ETP 085X95-Ø20 HL95

EAN 4031582318821
Order number 00801060



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	85 mm
Tread width	95 mm
Axle hole diameter	20 mm
Hub length	95 mm
Body width	95 mm
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D
Bearing type	6204

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Novatech
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	900 kg
Load capacity at 6 km/h	720 kg
Load capacity Static	1800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall weight	1.532 kg

NOVATECH

ETP 085X95-Ø20 HL95

EAN 4031582318821
Order number 00801060



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

