

PURETECH

PVR 160X40-Ø20

EAN 4031582321296
Broj porudžbine 00023492

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma crna
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	160 mm
Širina omotac	40 mm
dimenzija rupa osovina	20 mm
dužina glavcine	58 mm
Širina tela	40 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	135 kg
Statički Nosivost	270 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Ukupna težina	0,842 kg

PURETECH

PVR 160X40-Ø20

EAN 4031582321296
Broj porudžbine 00023492



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

