

SUPRATECH

PJR100x32-Ø12 HL44,4

EAN 4031582419306



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ○ ○
Movement Noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion Resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product Name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Electric Conductive	No
Stainless	No
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.14 kg

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Axle Hole Diameter	12 mm
Hub Length	44.4 mm

SUPRATECH

PJR100x32-Ø12 HL44,4

EAN 4031582419306



BETTER MOBILITY. BETTER LIFE.

Product Drawings

