

# ZETA

4688UOO200P63 WH-w46

EAN 4031582308341



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement Noise       | ● ● ● ● ●   |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion Resistance | ● ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product Name                | Zeta                          |
| Type                        | Fixed castor                  |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 4 km/h     | 600 kg                        |
| Load capacity at 6 km/h     | 480 kg                        |
| Electric Conductive         | No                            |
| Stainless                   | No                            |
| Load capacity Static        | 1200 kg                       |
| Temperature range (Minimum) | -30 °C                        |
| Temperature range (Maximum) | 80 °C                         |
| Overall Height              | 240 mm                        |
| Overall width               | 117 mm                        |
| Overall weight              | 1.81 kg                       |

## HOUSING

|                  |                         |
|------------------|-------------------------|
| Housing Material | Steel sheet, very heavy |
| Fork shape       | Broad, reinforced       |
| Housing Color    | Blue passivated         |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide                 |
| Tread Material Mix    | Identical with wheel body |
| Bearing               | Plain bearing             |
| Axle                  | Screwed with nut          |
| Wheel Color           | Natural white             |
| Threadguards          | Without threadguard       |
| Diameter              | 200 mm                    |
| Tread width           | 46 mm                     |
| Body width            | 46 mm                     |
| Hardness of tread (D) | 75 Shore D                |

## FITTING

|                             |                          |
|-----------------------------|--------------------------|
| Fitting type                | Medium rectangular plate |
| Plate length                | 137 mm                   |
| Plate width                 | 117 mm                   |
| Plate hole length (Minimum) | 75 mm                    |
| Plate hole length (Maximum) | 80 mm                    |
| Plate hole width (Minimum)  | 75 mm                    |
| Plate hole width (Maximum)  | 105 mm                   |
| Plate hole diameter         | 11 mm                    |

# ZETA

4688UOO200P63 WH-w46

EAN 4031582308341

Order number 00830083

Product Drawings



BETTER MOBILITY. BETTER LIFE.

