

NOVATECH

FTP 150X50-Ø20 HL60

EAN 4031582329452
Broj porudžbine 00800993

BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

| | |
|----------------------------|--------------------------|
| Materijal za telo | Ливено Гвожђе |
| materijal omotaca | Poliuretana, liveno |
| Nošenje | precizini kuglicni lezaj |
| Boja Tocak | Med žuta (RAL1005) |
| stitnici omotaca | Sa threadguard |
| Prečnik | 150 mm |
| Širina omotac | 50 mm |
| dimenzija rupa osovina | 20 mm |
| dužina glavcine | 60 mm |
| Širina tela | 50 mm |
| Teškoća gazećeg omotac (A) | 92 Šor A |
| Teškoća gazećeg omotac (D) | 42 Šor D |

PERFORMANSE

| | |
|------------------------|-----------|
| Performanse kotrljanja | ● ● ● ● ○ |
| Buka u pokretu | ● ● ● ○ ○ |
| Ishrana | ● ● ● ● ○ |
| otpornost na rdju | ● ● ● ○ ○ |

OSNOVNI ATRIBUTI

| | |
|--------------------------------|----------------------------------|
| Naziv proizvoda | Novatech |
| Tip | Tocak |
| Standard | EN12533 - Tockoviza teske terete |
| Nosivost na 4 km/h | 840 kg |
| Nosivost na 6 km/h | 700 kg |
| Statički Nosivost | 1400 kg |
| Temperaturni opseg (Minimalno) | -10 °C |
| Opseg temperature (maksimalni) | 60 °C |
| Ukupna težina | 2,446 kg |

NOVATECH

FTP 150X50-Ø20 HL60

EAN 4031582329452
Broj porudžbine 00800993



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

