

# NOVATECH

ETX082X70-Ø17 HL75-B

EAN 4031582331936



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

## TOCAK

Materijal za telo	Čelik, gvožđe
materijal omotaca	Poliuretana, liveno
Nošenje	precizini kuglični ležaj, zapečaceno
štitnici omotaca	Sa threadguard
Prečnik	82 mm
Širina omotac	70 mm
dimenzija rupa osovina	17 mm
dužina glavnice	75 mm
Teškoća gazećeg omotac (A)	92 Šor A
Tip ležaja	6303
Tip zaptivke	B
Pogodno za	jungheinrich_mic

## PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●●○

otpornost na rdju ●●●○○

## OSNOVNI ATRIBUTI

Naziv proizvoda Novatech

Tip Tocak

Nosivost na 3 km/h 700 kg

Statički Nosivost 1400 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

Ukupna težina 1,004 kg

# NOVATECH

ETX082X70-Ø17 HL75-B

EAN 4031582331936



BETTER MOBILITY. BETTER LIFE.

## TEHNIČKI CRTEŽI

