

FOOTMASTER

FOOT MASTER GASD-075-ASF-HUD

EAN 4031582495201
Order number 00800105



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

HOUSING

Offset	30 mm
Swivel radius	90 mm
Swivel interference	180 mm
Dome diameter	112 mm

FITTING

Plate length	112 mm
Plate width	112 mm
Plate hole length (Maximum)	92 mm
Plate hole width (Maximum)	92 mm
Plate hole diameter	9 mm

PERFORMANCE

Roll performance	○ ○ ○ ○ ○
Movement noise	○ ○ ○ ○ ○
Attrition	○ ○ ○ ○ ○
Corrosion resistance	○ ○ ○ ○ ○

CORE ATTRIBUTES

Product name	Footmaster
Type	Swivel castor
Load capacity at 3 km/h	250 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	90 °C
Overall height	120 mm
Overall width	128 mm
Overall weight	6.97 kg

WHEEL

Bearing	Unmachined hub
Diameter	75 mm
Tread width	30 mm
Body width	30 mm

FOOTMASTER

FOOT MASTER GASD-075-ASF-HUD

EAN 4031582495201
Order number 00800105



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

