

ELASTECH

IFP160X50-Ø20

EAN 4031582319811
Order number 00805136



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Aluminum
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Precision ball bearing
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.36 in
Body width	1.97 in
Hardness of tread (A)	68 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	771.62 lb
Load capacity at 3.7 mph	617.29 lb
Load capacity Static	1543.23 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	2.65 lb

ELASTECH

IFP160X50-Ø20

EAN 4031582319811
Order number 00805136



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

