

ELASTECH

UFR160X46-Ø20 BLUE TFR

EAN 4031582394535



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Elastic tire, non-marking, vulcanized
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	160 mm
Tread width	46 mm
Axle hole diameter	20 mm
Hub length	58 mm
Hardness of tread (A)	64 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	300 kg
Load capacity Static	600 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	80 °C
Overall weight	0.818 kg

ELASTECH

UFR160X46-Ø20 BLUE TFR

EAN 4031582394535



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

