

LINEA LIGHT

5920UOI065L51-10

EAN 4031582404081



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ●●●○○

Buka u pokretu ●●●○○

Ishrana ●●●○○

otpornost na rdju ●●●●○

OSNOVNI ATRIBUTI

Naziv proizvoda Linea light

Tip Okretanje Tocak

Standard EN12528 - tockovi za namestaj

Nosivost na 3 km/h 50 kg

Statički Nosivost 100 kg

Temperaturni opseg (Minimalno) -10 °C

Opseg temperature (maksimalni) 40 °C

Sveukupna visina 68 mm

Ukupna širina 46 mm

Ukupna težina 0,087 kg

TOCAK

Materijal za telo	poliamid
materijal omotaca	Identično sa telom Tocak
Nošenje	klizni lezaj sa caura cevi
stitnici omotaca	Bez stražara
Prečnik	65 mm
Širina omotac	13,9 mm

KUCISTE

Materijal	poliamid
oblik viljuska	kuciste za dva Tocak
okretni lezaj	stablo , okretanje
okretni radijus	56 mm
Otpor okretanju	112 mm
Prečnik kupole	23 mm

PRILAGOĐAVANJE

Tip uklapanja	zatvorena rupa za postavljanje B10
dimenzija rupa sraf	10 mm

Deutscher
dizajner
ClubInterzum
nagradaIF nagrada za
Dizajn

LINEA LIGHT

5920UOI065L51-10

EAN 4031582404081



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

