

# STYLEA

5920UJI075B10-11X20

EAN 4031582456196



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	3.19 in
Overall width	2.09 in
Overall weight	0.39 lb

## WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.31 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.44 in
Swivel interference	4.88 in
Dome diameter	0.87 in

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in

PRODUCT INFORMATION

# STYLEA

5920UJI075B10-11X20

EAN 4031582456196



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

