

ALPHA STAINLESS

8470IDG100P30-13 TREAD-1023

EAN 4031582373097
Order number 00061133



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ● ●
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Alpha stainless
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	176.37 lb
Stainless	✓
Load capacity Static	352.74 lb
Temperature range (Minimum)	-13 °F
Temperature range (Maximum)	266 °F
Overall height	5.04 in
Overall width	2.95 in
Overall weight	2.13 lb

WHEEL

Body material	Aluminum
	soft
Tread material	Damping, heat resistant
Bearing	Dry bearing bush
Axle	Screwed with nut
Wheel color	Metallic
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.38 in
Body width	1.38 in
Hardness of tread (A)	75 Shore A

HOUSING

Material	Stainless steel, heavy
Fork shape	Broad
Swivel bearing	Two ball races
Color	Stainless steel
Offset	1.61 in
Swivel radius	3.58 in
Swivel interference	7.17 in
Dome diameter	2.95 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in

ALPHA STAINLESS

8470IDG100P30-13 TREAD-1023

EAN 4031582373097
Order number 00061133



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

8470U0D100P30- ϕ 11

