

# STYLEA

5920UJI075B10-11X20

EAN 4031582456196



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

## CORE ATTRIBUTES

Product name	Stylea
Housing type	Swivel castor
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	81 mm
Overall width	53 mm
Overall weight	0.177 kg

## WHEEL

Body material	Polyamide
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	8 mm
Hardness of tread (A)	87 Shore A

## HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	62 mm
Swivel interference	124 mm
Dome diameter	22 mm

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

PRODUCT INFORMATION

# STYLEA

5920UJI075B10-11X20

EAN 4031582456196



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

