PRODUCT INFORMATION

AGILA

2478UAP050P41-55

EAN 4031582404326

BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Agila
Type	Fixed caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	no
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.72 in
Overall width	1.38 in
Overall weight	0.24 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Housing Color	Blue passivated
Dome diameter	1.06 in

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Wheel color	Silver gray (RAL7001)
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

FITTING

Fitting type	Square plate
Plate length	2.17 in
Plate width	2.17 in
Plate hole length (Minimum)	1.52 in
Plate hole length (Maximum)	1.73 in
Plate hole width (Minimum)	1.52 in
Plate hole width (Maximum)	1.73 in
Plate hole diameter	0.25 in

© Copyright 2026 TENTE International GmbH


AGILA


2478UAP050P41-55


EAN 4031582404326

Order number 00039979

Product Drawings







© Copyright 2026 TENTE International GmbH