

PURETECH

PIR100X35-Ø12 HL44,4

EAN 4031582320336

Broj porudžbine 00030826



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja ● ● ● ○ ○

Buka u pokretu ● ● ● ● ○

Ishrana ● ● ● ○ ○

otpornost na rdju ● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda Puretech

Tip kućišta Tocak

Standard EN12532 - transportna oprema

Nosivost na 4 km/h 75 kg

Statički Nosivost 150 kg

Temperaturni opseg (Minimalno) -20 °C

Opseg temperature (maksimalni) 60 °C

Ukupna težina 0,283 kg

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	kotrljajući lezaj
Boja Tocak	Grafitna crna (RAL9011)
stitnici omotaca	Bez stražara
Prečnik	100 mm
Širina omotac	35 mm
dimenzija rupa osovina	12 mm
dužina glavcine	44,4 mm
Širina tela	35 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PURETECH

PIR100X35-Ø12 HL44,4

EAN 4031582320336
Broj porudžbine 00030826



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

