

# ZETA REVERSE

468BTOP160P63

EAN 4031582398472  
Order number 00860871



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                                                                  |
|-----------------------------|------------------------------------------------------------------|
| Product name                | Zeta reverse                                                     |
| Housing type                | Swivel castor with total lock and spring loaded directional lock |
| Standard                    | EN12532 - Transport Equipment                                    |
| Load capacity at 4 km/h     | 800 kg                                                           |
| Load capacity at 6 km/h     | 640 kg                                                           |
| Load capacity Static        | 1600 kg                                                          |
| Temperature range (Minimum) | -30 °C                                                           |
| Temperature range (Maximum) | 80 °C                                                            |
| Overall height              | 200 mm                                                           |
| Overall width               | 96 mm                                                            |
| Overall weight              | 3.633 kg                                                         |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polyamide, heavy          |
| Tread material        | Identical with wheel body |
| Bearing               | Precision ball bearing    |
| Axle                  | Screwed with nut          |
| Wheel color           | Natural white             |
| Threadguards          | Without threadguard       |
| Diameter              | 160 mm                    |
| Tread width           | 50 mm                     |
| Body width            | 50 mm                     |
| Hardness of tread (D) | 75 Shore D                |

## HOUSING

|                     |                                         |
|---------------------|-----------------------------------------|
| Material            | Steel sheet, very heavy                 |
| Fork shape          | Broad, reinforced                       |
| Swivel bearing      | Two ball races, reinforced or stainless |
| Colour              | Blue passivated                         |
| Offset              | 55 mm                                   |
| Swivel interference | 322 mm                                  |
| Dome diameter       | 96 mm                                   |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 137 mm            |
| Plate width                 | 105 mm            |
| Plate hole length (Minimum) | 75 mm             |
| Plate hole length (Maximum) | 80 mm             |
| Plate hole width (Minimum)  | 75 mm             |
| Plate hole width (Maximum)  | 105 mm            |
| Plate hole diameter         | 11 mm             |

# ZETA REVERSE

468BTOP160P63

EAN 4031582398472  
Order number 00860871



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

