

# SUPRATECH

PJR100X32-Ø12 HL44,4

EAN 4031582419306



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	100 mm
Tread width	32 mm
Axle hole diameter	12 mm
Hub length	44.4 mm

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Supratech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	80 kg
Load capacity Static	160 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.136 kg

# SUPRATECH

PJR100X32-Ø12 HL44,4

EAN 4031582419306



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

