

EXPANDER

R47-Ø32-35 Inox_TBE

EAN 4031582437904



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	1.26 in
Expander fitting (Maximum)	1.38 in
Hint	Please indicate required tube innerdiameter when ordering.

PERFORMANCE

Corrosion resistance	● ● ● ○ ○
----------------------	-----------

CORE ATTRIBUTES

Product name	Expander
Type	Accessory
Electric conductive	no
Stainless	Yes
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall weight	0.31 lb