

P11-40X27 / 8

EAN 4031582320213



Image may differ from the original product

PERFORMANCE

Corrosion resistance ● ● ● ○ ○

CORE ATTRIBUTES

Product name	Accessory
Housing type	Accessory
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Overall height	8 mm

FITTING

Fitting type	Stem with L-shaped plate
Plate length	40 mm
Plate width	27 mm
Plate hole length (Maximum)	32 mm
Plate hole width (Maximum)	32 mm
Plate hole diameter	4 mm