

ALPHA STAINLESS

8470PIO080P30-13

EAN 4031582381573



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

PERFORMANSE

Performanse kotrljanja	● ● ● ● ○
Buka u pokretu	● ● ● ● ○
Ishrana	● ● ● ● ○
otpornost na rdju	● ● ● ● ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Alpha stainless
Tip	Okretanje Tocak
Standard	EN12532 - transportna oprema
Nosivost na 4 km/h	70 kg
Električni provod	no
nerdjajuci	yes
Statički Nosivost	140 kg
Temperaturni opseg (Minimalno)	-20 °C
Opseg temperature (maksimalni)	60 °C
Sveukupna visina	108 mm
Ukupna težina	0.72 kg

KUCISTE

Materijal kućišta	nerdjajuci čelik, težak
oblik viljuska	siroko
okretni lezaj	Dve lopte
Boja	nerdjajuci čelik
ofset	44.5 mm
okretni radijus	84.5 mm
Otpor okretanju	169 mm

TOCAK

Materijal za telo	polipropilen
materijal omotaca	Cvrsta guma, bez obeležavanja
Nošenje	klizni lezaj
osovina	Završena sa navrtkom
stitnici omotaca	Bez stražara
Prečnik	80 mm
Širina omotac	35 mm
Teškoća gazećeg omotac (A)	80 Šešelj A

PRILAGOĐAVANJE

Tip uklapanja	otvor za vijak
dimenzija rupa sraf	13 mm

ALPHA STAINLESS

8470PIO080P30-13

EAN 4031582381573



BETTER MOBILITY. BETTER LIFE.

Product Drawings

