

ZETA REVERSE

468BTOO125P63 180°

EAN 4031582398205
Order number 00860931



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ○ |
| Movement noise | ● ○ ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--|
| Product name | Zeta reverse |
| Housing type | Swivel castor with total lock and spring loaded directional lock |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph | 1543.23 lb |
| Load capacity at 3.7 mph | 1234.59 lb |
| Load capacity Static | 3086.47 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 6.46 in |
| Overall weight | 6.28 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing |
| Axle | Screwed with nut |
| Threadguards | Without threadguard |
| Diameter | 4.92 in |
| Tread width | 1.97 in |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|---|
| Material | Steel sheet, very heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Two ball races, reinforced or stainless |
| Offset | 2.36 in |
| Swivel interference | 14.17 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 5.39 in |
| Plate width | 4.13 in |
| Plate hole length (Maximum) | 4.13 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 3.15 in |
| Plate hole diameter | 0.43 in |

ZETA REVERSE

468BTOO125P63 180°

EAN 4031582398205
Order number 00860931



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

