

DURATECH

UOP250X50-Ø25 TFR

EAN 4031582390667



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polyamide
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	250 mm
Tread width	50 mm
Axle hole diameter	25 mm
Hub length	60 mm
Hardness of tread (D)	75 Shore D

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Duratech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	1000 kg
Load capacity Static	2000 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall weight	1.3 kg

DURATECH

UOP250X50-Ø25 TFR

EAN 4031582390667



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

