

# ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333  
Order number 00830872



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Steel, iron
Tread material	Elastic tire, black, vulcanized
Bearing	Borehole, unmachined
Wheel color	Jet black (similar RAL9005)
Diameter	7.87 in
Tread width	2.95 in
Axle hole diameter	3.94 in
Hub length	2.95 in
Body width	2.95 in
Hardness of tread (A)	68 Shore A

## PERFORMANCE

Roll performance	● ● ○ ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Elastech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	1322.77 lb
Load capacity at 3.7 mph	1102.31 lb
Load capacity Static	2204.62 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall weight	5.08 lb

# ELASTECH

EEZ 200X75-Ø100 DG

EAN 4031582318333  
Order number 00830872



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

