

MAXTECH

DNP400X90-Ø10 NL129 YELLOW WITH AXLE

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	15.75 in
Tread width	3.54 in
Axle hole diameter	0.39 in
Hub length	5.08 in

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Housing type	Wheel
Load capacity at 1.8 mph	319.67 lb
Load capacity Static	418.88 lb
Overall weight	7.98 lb

MAXTECH

DNP400X90-Ø10 NL129 YELLOW WITH AXLE

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

