

MAXTECH

DNP400X90-Ø10 NL129 YELLOW WITH AXLE

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|--------------------|------------------------|
| Body material | Sheet Steel |
| Tread material | Polyurethane, foamed |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 15.75 in |
| Tread width | 3.54 in |
| Axle hole diameter | 0.39 in |
| Hub length | 5.08 in |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|--------------------------|-----------|
| Product name | Maxtech |
| Type | Wheel |
| Load capacity at 1.8 mph | 319.67 lb |
| Load capacity Static | 418.88 lb |
| Overall weight | 7.98 lb |

MAXTECH

DNP400X90-Ø10 NL129 YELLOW WITH AXLE

EAN 4031582438208



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

