

PURETECH

DVR080X20-Ø8X45,5 + ASBUS

EAN 4031582331653



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	20 mm
Axle hole diameter	8 mm
Hub length	45.5 mm
Hardness of tread (A)	85 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ○ ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.272 kg

PURETECH

DVR080X20-Ø8X45,5 + ASBUS

EAN 4031582331653



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

