

PURETECH

PVR 300X50-Ø20 HL58

EAN 4031582321357
Order number 00038262



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, black
Bearing	Roller bearing
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	11.81 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.28 in
Body width	1.97 in
Hardness of tread (A)	80 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Puretech
Type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	551.16 lb
Load capacity Static	1102.31 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	6.22 lb

PRODUCT INFORMATION

PURETECH

PVR 300X50-Ø20 HL58

EAN 4031582321357
Order number 00038262



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

