

# COMPACTA

1530PJO040P41

EAN 4031582425376



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## CORE ATTRIBUTES

Product name	Compacta
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	44.09 lb
Load capacity Static	88.18 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.01 in
Overall weight	0.15 lb

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	1.57 in
Tread width	0.91 in
Hardness of tread (A)	87 Shore A

## HOUSING

Material	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	0.75 in
Swivel radius	1.54 in
Swivel interference	3.07 in

## FITTING

Fitting type	Square plate
Plate length	1.46 in
Plate width	1.46 in
Plate hole length (Maximum)	1.18 in
Plate hole width (Maximum)	1.18 in