

BASETECH

POR100X36-Ø12 WHITE TFR

EAN 4031582390599



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	3.94 in
Tread width	1.42 in
Axle hole diameter	0.47 in
Hub length	1.75 in
Hardness of tread (D)	69 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	352.74 lb
Load capacity Static	705.48 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	0.32 lb

BASETECH

POR100X36-Ø12 WHITE TFR

EAN 4031582390599



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

