

BASETECH

POR080X34-Ø12 RAL9011

EAN 4031582320763
Order number 00030950



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Roller bearing
Threadguards	Without threadguard
Diameter	80 mm
Tread width	34 mm
Axle hole diameter	12 mm
Hub length	44.4 mm
Hardness of tread (D)	65 Shore D

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Basetech
Housing type	Wheel
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	125 kg
Load capacity Static	250 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.102 kg

PRODUCT INFORMATION

BASETECH

POR080X34-Ø12 RAL9011

EAN 4031582320763
Order number 00030950

TECHNICAL DRAWINGS

