

PURETECH AIR

DQP400X100-Ø20 HL74 4PR

EAN 4031582318029



BETTER MOBILITY. BETTER LIFE.



Slika se može razlikovati od originalnog proizvoda

TOCAK

Materijal za telo	Čelik lista
	mekan
materijal omotaca	Pneumatička guma, profil bloka
Nošenje	precizini kuglicni lezaj
stitnici omotaca	Sa threadguard
Prečnik	400 mm
Širina omotac	100 mm
dimenzija rupa osovina	20 mm
dužina glavcine	74 mm
Teškoća gazećeg omotac (A)	55 Šor A

PERFORMANSE

Performanse kotrljanja	● ● ● ○ ○
Buka u pokretu	● ● ● ○ ○
Ishrana	● ● ● ○ ○
otpornost na rdju	● ● ● ○ ○

OSNOVNI ATRIBUTI

Naziv proizvoda	Puretech air
Tip	Tocak
Nosivost na 3 km/h	200 kg
Statički Nosivost	400 kg
Ukupna težina	2,665 kg

PURETECH AIR

DQP400X100-Ø20 HL74 4PR

EAN 4031582318029



BETTER MOBILITY. BETTER LIFE.

TEHNIČKI CRTEŽI

